



**BLONDER  
TONGUE**  
LABORATORIES, INC.

# MIPS-12D

## HE-12 SERIES POWER SUPPLY

MIPS-12D HE-12 Series Power Supply now with higher current capacity.

Powers any combination of HE Series modules when mounted in a MIRC-12V rack chassis.



### FEATURES

- Upgraded current capacity
- 27% higher on 5 VDC
- 11% higher on 12 VDC
- Fan cooled
- Wide AC input range

### ORDERING INFORMATION

Model	Stock #	Description
MIPS-12D	7722D	HE-12 Series Power Supply

# SPECIFICATIONS

## INPUT

<b>MIPS</b>	
<b>Connectors:</b>	IEC
<b>AC Voltage Range:</b>	100 VAC to 240 VAC ± 10%
<b>AC Frequency:</b>	50 to 60 Hz

## OUTPUT

<b>MIPS</b>	
<b>Connectors</b>	37 pin D
<b>DC Power Output:</b>	5 VDC @ 7.0A
	12 VDC @ 4.5A

## GENERAL

<b>Dimensions (W x D x H):</b>	4.2 x 3.5 x 7.5 inches (106 x 89 x 190 mm)
<b>Weight:</b>	2.6 lbs (1.2 kg)
<b>Operating Temperature:</b>	32 to 122 °F (0 to 50 °C)
<b>Storage Temperature:</b>	-13 to 158 °F (-25 to 70 °C)
<b>Operating Humidity:</b>	0 to 95% RH @ 35 °C max, non-condensing
<b>Storage Humidity:</b>	0 to 95% RH @ 35 °C max, non-condensing

## ALARMS/MONITORING/CONTROL

<b>Front Panel</b>	
<b>Power Indicator:</b>	Green LED

# RELATED PRODUCTS

Model	Description
MIRC-12V	HE Series vented rack chassis