

## ETP-400C – Single Button Assistance Phone

### Description


The **ETP-400C** is an outdoor-rated, ADA-compliant hands-free Emergency Phone for use in locations such as: parking facilities, college campuses, controlled access gates, medical centers and industrial parks.

### Features

- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal button
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
- Push button once to call, then speak hands-free
- Circuit boards are conformally coated for water protection
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



### Specifications

Construction:	12 gauge (2.8mm) #4 brushed stainless steel faceplate
Dimensions:	Front Panel: 9.5(241) W x 11.75(298) H in(mm) Wall Opening: 6.63(168) W x 9.75(248) H x 2.5(64) D in(mm)
Weight:	8 lbs. (3.6 kg)
Operating Temperature:	-4°F to +149°F (-20°C to +65°C)
Mounting:	Flush mounts (surface mount options available)
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightning suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1-minute increments.
Wiring Requirements:	1 twisted-shielded pair
Compliance:	CSA Certified to UL Standard 60950 


### Options & Accessories

Voice Location Identifier:	Model <b>ETP-400CV</b> includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming.
"EMERGENCY" Casting:	Use Model <b>ETP-400</b> for a button that reads <b>EMERGENCY</b> instead of TO CALL
Mounting Sleeve:	Use Model <b>MS-400</b> to mount flush into wall
8-Line Consolidator:	Model <b>EC-8</b> allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines.
Monitoring/Diagnostic Software Package:	Talk-A-Lert®, model <b>ETP-TAL</b> , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events

Copyright 2009 Talk-A-Phone Co. All rights reserved.

# ETP-400C – Single Button Outdoor Assistance Phone

## Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804  
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com  
All prices and specifications are subject to change without notice.  
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.