



## RHW75 Vandal-Resistant Dome

Ideal for applications needing extra protection from vandalistic attacks, Moog Videolarm's 7" vandal-resistant, rugged housing (RHW75 Series) offers versatility and adequate camera protection in a compact/attractive design. Constructed of a cast aluminum top, and polycarbonate dome, the RHW75 Series boasts an IP66 rating. The RHW75 Series is available in a variety of models, designed to suit your individual needs. Select from one of our outdoor or indoor, wall or pendant mount options. The RHW75 Series includes Moog Videolarm's universal camera bracket system which enables you to utilize most of today's leading IP or analog camera systems (fixed or PTZ). Outdoor models include two heaters and two blowers.

### Key Features

- Rugged, vandal-resistant cast aluminum top and polycarbonate dome
- Equipped with a thermostatically controlled Heater system and a sustaining Air Circulation Fan, the Fusion Dome allows efficient dome views during every season
- Comes standard with wall mount; optional pendant mount available
- Meets IP66 standards for dust and water penetration (pendant mount)
- Indoor & outdoor models; outdoor models include two heaters/blowers
- Great for monitoring applications: parking lots, high crime areas, schools



## Outdoor / Indoor PTZ Camera:

### RHW75C2N / IRHP75TN / RHW75C12N

The **RHW75C2N** is a IP network ready 7" vandal-resistant outdoor dome housing with wall mount, rugged aluminum top and polycarbonate clear dome, with 24Vac input, heater/blower, for an IP network PTZ camera, 120 to 24Vac transformer. The **IRHP75TN** is the indoor version of the RHW75C2N and has no electronics. The **RHW75C12N** is the 12Vdc version of the RHW75C2N

## Outdoor/Indoor Fixed Camera:

### RHW75CF2N

The **RHW75CF2N** is a IP network ready 7" vandal-resistant outdoor dome housing with wall mount, rugged cast aluminum top and polycarbonate clear dome, with 24Vac input, heater/blower, for an IP network fixed camera, 120 to 24Vac transformer. The **IRHP75TF** is the indoor version with no electronics

Tinted and Clear domes available specify "C" for Clear or "T" for Tinted. Wall Mounts and Pendant Mounts available specify "W" for Wall Mount or "P" for Pendant Mount



## ACCESSORIES:



### PB24

Rugged cast aluminum power box with 84vA and 24vA power supply



### APM3

Aluminum pole mount bracket with female inserts



### SSY7

Sunshield for RH7 or FusionDome FD7 housing

## COMPATIBLE CAMERAS:

To view the latest listing of compatible cameras please visit [www.videolarm.com/thirdparty.jsp](http://www.videolarm.com/thirdparty.jsp)

### PTZ:



ACM-8201/8211, ACM-8511, CAM-6510



213, 214, 215, 231D, 232D, 233D



VB-C300, VB-C50i, VB-C60, VC-C50i



dcs 5000 Series, dcs 6600 Series



PTC-200C, PTC-400C, PTC-401C IP



iCanView 250/252



VN-C625U, VN-V685U, VN-V686BU, VN-V686U



BB-HCE381A, BB-HCE481A, BB-HCE580A, BB-HCE581A, BB-HCE581A-W, WV-NS202A



SNC-RH124, SNC-RS44/46, SNC-RX530/550/570, SNC-RZ25, SNC-RZ30, SNC-RZ50



IK-WB21A

FIXED COMPATIBLE CAMERAS ALSO AVAILABLE

For detailed list see web site\*\*\*\*

## SPECIFICATIONS:

Mechanical Specifications	
Size (h*w*d):	14.7" x 8.2" x 14.5" (374 x 208 x 369mm)
Weight:	13 Lbs. (6 Kg.)
Construction	TOP: 3mm engineered plastic
	DOMES: Polycarbonate
Mount Bracket:	Machined & cast aluminum

Electrical Specifications	
Power Requirements	
Standard Outdoor Model:	24Vac 52W
Network Outdoor Model:	24Vac, 80W (includes 20W for heater)

Environmental Specifications	
Operating Temperature:	-40°F to 120°F (-40°C to 49°C)
Meets IK10 Specifications	

Shipping Specifications		
MODEL	SHIPPING WEIGHT	BOX DIMENSIONS
RHW75	14 Lbs. (6.4 Kg.)	17" x 14" x 17" (431.8 x 355.6 x 431.8mm)

## Certifications and Ratings

UL Listed	WEEE	CE	RoHS

## Architectural Drawings

