




SPECIFICATIONS:

DIMENSIONS : 84.0"H (86.0"H w/ OPTIONAL CASTERS) x 30.0"W x 42.0"D

RACK SPACES : 44 RMU w/ NUMBERED RMU INDICATORS, 19" EIA 310-E COMPLIANT.

WEIGHT CAPACITY : 2000 lbs. BOLTED TO FLOOR OR ON LEVELERS, 1800 lbs. ON CASTERS.

COLOR : DURABLE TEXTURED BLACK POWDER COATING

CERTIFICATIONS : UL 60950-1 STANDARD FOR I.T. & COMMUNICATIONS EQ., ENCLOSURES.

CONSTRUCTION : 2 PAIR MOUNTING RAILS , #12 GA. C.R.S.
FULLY WELDED FRAME, #14 & #12 GA. C.R.S.
DOORS, SIDE PANELS, TOP PANEL, #16 C.R.S.

HARDWARE : PACKAGE OF QTY-50; M6 SCREWS AND CAGE NUTS, INCLUDED.

INTERPRET DRAWING PER ASME Y14.5M-1994	
DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH	DRAWING NOT TO SCALE
TOLERANCE UNLESS OTHERWISE NOTED:	
ANGULAR +/- .1°	XXX +/- .010
XXX +/- .015	XX +/- .020
XX +/- .030	X FOR REF. ONLY
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES	

NOTICE:	
Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.	

PART NUMBER: 8401ES-3042	TITLE: ENHANCED SERVER ENCL., 44 RMU, 19" EIA	
QTY PER UNIT: 1	GREAT LAKES CASE & CABINET CO., INC.	
MATERIAL TYPE: -	P.O. BOX 551 EDINBORO, PA 16142	
MATERIAL GAUGE: -	PHONE: (814) 734-7303 FAX: (814) 734-3907	
FINISH: -	E-MAIL: glcc@greatlakes.com	
DRAWN BIBS	DATE 6/1/2007	DWG NO. 840ES-3042MS
CHECKED & APP. WSS	DATE 9/24/07	REV -
		SHEET: 1 OF 1