


Part Number.....7215

Made in the USA..... Yes
Mounting..... Vertical
AC Rating Volts..... 125
AC Rating Amps..... 15
AC Rating Watts..... 1800
AC Rating Frequency-Hz..... 50/60 HZ
Circuit Breaker..... 15A
Pilot Light..... Green
On/Off Switch..... None
Over Current Protection..... CB
Power Cable AWG..... 14/3 SJT
Power Cable Length..... 15'
Plug Type..... NEMA 5-15P
Receptacle Type..... NEMA 5-15R
Receptacle Style..... Single
Receptacle Quantity..... 16
Max. Output per Powerstrip..... 15 Amp
Joule Rating..... N/A
UL Rating..... 60950-1
Clamping Level..... N/A
Response Time..... N/A
Max. Surge Current..... N/A
EMI/RFI Noise Reduction..... N/A
Surge Indicator Red LED..... N/A
Connected Equipment Warranty.... N/A
Product Warranty-GLCC..... 1 year
Certification/Agency Approvals..... UL & CSA Approved
Unit Weight lbs..... 6



NOTE: UL & CSA APPROVED

Rev.	Date	Dr.	CKD/APPD.	Description
A		TK	-	CHANGED SWITCH TO PILOT LIGHT

TOLERANCES UNLESS OTHERWISE SPECIFIED		Dr. T. KAUPP	Rev. 06-14-99	Title 7215 GREAT LAKES
DECIMALS		CKD	Rev.	
0.0 = ± 0.100		APPD.	Rev.	
0.00 = ± 0.005		SCALE	SHT 1 of 1	
0.000 = ± 0.0005				
ANGLES = ± 1°				
Great Lakes cable & cabinet co., inc.				DWG No. 7215.dwg
				Rev. -