





REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
0	ECO-02770	1/28/2010	WSS
1	ECO-03097	1/11/2011	MZ



FRONT VIEW




RIGHT SIDE VIEW



			Bill of Material		
ITEM	PART NUMBER	QTY	DESCRIPTION	FILE NAME	REVISION
1		2	BASE ANGLE FOR GLRR-1984 RELAY RACK	I002709.ipt	5
2	500-13X1HHB	12	BOLT, 1/2"-13 x 1" HEX HD	500-13X1HHB.ipt	-
3	500SPLWSHR	12	WASHER, 1/2" SPLIT LOCK, STEEL	500SPLWSHR.ipt	-
4	GL-NAMEPLATE	1	GLCC NAME PLATE, AL., 3" x .75" w/ "3MLSE9495" ADHESIVE, LaFrance Corp.	GL-NAMEPLATE.ipt	-
5		2	VERTICAL CHANNEL FOR 108"H TWO POST RACK	I011473.ipt	0
6		2	TOP ANGLE FOR GLRR-1984 RELAY RACK	I002710.ipt	7
7		1	PACKAGING MATERIAL FOR 108"H TWO POST RACK	-	-
8		1	ASSEMBLY INSTRUCTION: FORM #05-10	-	-
9	12/24X1/223SC	50	#12-24 x 1/2"L PAN HD PHIL TYPE 23 ZN PL SCREW	-	-

GLCC PART NO:	FINISH
GLRR19108BAX200	BLACK ANODIZED
GLRR19108AEX200	ACID ETCHED & ANODIZED

- SPECIAL NOTES:**
- ATTACH CAUTION LABEL ON ONE OF THE BASE ANGLES - CENTERED. THE LABEL SHOULD STATE: "CAUTION - RACK MUST BE FIRMLY ANCHORED TO FLOOR. CONCRETE FLOOR SURFACE RECOMMENDED."
 - TWO POST RACK TO BE SHIPPED UNASSEMBLED.
 - SHIPPING BOX TO CONTAIN ONE PACK OF (50) #12-24 x 1/2"L MOUNTING SCREWS AND AN ASSEMBLY INSTRUCTION.



VIEW A-A
SCALE .25



DETAIL B
INSTALL ITEM #4 AS SHOWN.
ONE LABEL CENTERED
ON ONE OF TOP ANGLES.

INTERPRET DRAWING PER ASME Y14.5M-1994		NOTICE:		PART NUMBER: GLRR19108 (SEE TABLE)		TITLE 19"EIA ALUMINUM TWO POST RACK, 108"H	
DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH		Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.		QTY PER UNIT: 1		GREAT LAKES CASE & CABINET CO., INC. P.O. BOX 551 EDINBORO, PA 16412 PHONE (814) 734-7303 FAX (814) 734-3907 E-MAIL glcc@greatcabinets.com	
DRAWING NOT TO SCALE				MATERIAL TYPE: -			
TOLERANCE UNLESS OTHERWISE NOTED: ANGULAR +/- .1" .XXXX +/- .010 .XXX +/- .015 .XX +/- .030 X FOR REF. ONLY				MATERIAL GAUGE: -			
				FINISH: SEE NOTES			
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES		DRAWN JAL		DATE 12/9/2004	DWG NO: I011471	REV 1	SHEET: 1 OF 1
		THIRD ANGLE PROJECTION		CHECKED & APP. WSS	DATE 1/28/2010		