

Power up to 4 Wireless Access Points or Other PoE-capable Devices



- Senses and adjusts for network speed and cabling type
- Durable case and silent, fan-less design
- Auto power-down mode saves energy when port is unused
- Auto Green mode detects cable length and adjusts power usage

Features

- Fast, auto-switching Ethernet connection integrates 10, 100, and 1,000 Mbps devices into your network
- Supports Windows® and Macintosh® platforms
- LEDs make it easy to monitor link, speed, and activity
- AutoUplink™ technology automatically adjusts for two common types of cables




NETGEAR Green

- Auto power-down mode saves energy when port is unused
- Auto Green mode detects cable length and adjusts power usage to save energy

Features	FS105	FS108	FS116	FS108P	FS116P	GS105	GS108	GS108P	GS116	JFS516	JFS524	JGS516	JGS524
10/100 Mbps Ports	5	8	16	8	16					16	24		
10/100/1000 Mbps Ports						5	8	8	16			16	24
Auto Uplink™	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙
Internal Power Supply										⊙	⊙	⊙	⊙
Metal Enclosure	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙
Port LEDs	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙				
Rack Mountable										⊙	⊙	⊙	⊙
Power over Ethernet (PoE)				4	8			4					
Warranty [†]	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime	Lifetime





Technical Specifications

• Network Protocol and Standards Compatibility

- IEEE 802.3i 10BASE-T
- IEEE 802.3u 100BASE-TX
- IEEE 802.3ab 1000BASE-T Gigabit Ethernet
- IEEE 802.3x flow control
- IEEE 802.3af DTE power via MDI

• Power Supply

- Total power consumption: 60W maximum
- 802.3af power consumption: 50W maximum (ports 1–4)
- 48V DC, 1.25A power output; plug is localized to country of sale

• Network Ports

- 8 auto speed-sensing 10/100/1000 RJ-45 ports

• Physical Specifications

- Dimensions (H x W x D):
27 x 235 x 103 mm (1.1 x 9.3 x 4.1 in)
- Weight: 0.716 kg (1.7 lb)

• Performance Specifications

- Forwarding mode: Store-and-forward
- Queue buffer memory: 192 KB per port
- Bandwidth: 16 Gbps (non-blocking)
- Forwarding rate:
 - 10 Mbps port: 14,880 packets/sec
 - 100 Mbps port: 148,800 packets/sec
 - 1000 Mbps port: 1,488,000 packets/sec
- Latency (using 1500-byte packets):
 - 10 Mbps: 30μs (max)
 - 100 Mbps: 6μs (max)
 - 1000 Mbps: 4μs (max)
- MAC address database: 4K

• Electromagnetic Emissions

- CE mark, commercial
- FCC Part 15 Class B
- VCCI Class B
- C-Tick
- EN 55022 (CISPR 22) Class B

• Environmental Specifications

- Operating temperature: 32° to 122° F (0° to 50° C)
- Storage temperature: -4° to 158° F (-20° to 70° C)
- Operating humidity: 90% maximum relative humidity, non-condensing
- Storage humidity: 95% maximum relative humidity, non-condensing
- Operating altitude: 10,000 ft (3,000 m) maximum
- Storage altitude: 10,000 ft (3,000 m) maximum

• Status LEDs

- System: Power, PoE maximum power
- Per port: Link, activity, speed, PoE active, PoE fault

• Safety

- CE mark, commercial
- CE/LVD EN 60950

System Requirements

- Category 5 UTP network cables or above
- Network card for each PC
- Network software (e.g., Windows®)
- Web browser (e.g., Internet Explorer 5.0 or higher, Netscape 6.0 or higher)

Warranty

- NETGEAR Lifetime Warranty†
- Power supply: NETGEAR 2-year Warranty

ProSupport Service Packs Available

- **OnCall 24x7, Category 1**
 - PMB0331-100 (US)
 - PMB0331 (non-US)
- **XPressHW, Category 1**
 - PRR0331

Package Contents

- ProSafe® 8-port 10/100/1000 Gigabit Switch with 4-port PoE (GS108P)
- AC adapter
- Wall-mount kit
- Installation guide
- Warranty/support information card

Ordering Information

- North America: GS108P-100NAS
- Europe: GS108P-100EUS
- Asia: GS108P-100PES

NETGEAR®

350 E. Plumeria Drive
San Jose, CA 95134-1911
1-888-NETGEAR (638-4327)
E-mail: info@NETGEAR.com
www.NETGEAR.com

© 2009 NETGEAR, Inc. NETGEAR, the NETGEAR Logo, NETGEAR Digital Entertainer Logo, Connect with Innovation, FrontView, IntelliFi, PowerShift, ProSafe, ProSecure, RAIDar, RAIDiator, RangeMax, ReadyNAS, Smart Wizard, X-RAID, and X-RAID2, are trademarks and/or registered trademarks of NETGEAR, Inc. and/or subsidiaries in the United States and/or other countries. Mac and the Mac logo are trademarks of Apple Inc., registered in the U.S. and other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. All rights reserved.

This product comes with a limited warranty, the acceptance of which is a condition of sale. This product has been tested for quality assurance and this product or its components may have been recycled.

*Basic technical support provided for 90 days from date of purchase.

†Lifetime warranty for product purchased after 05/01/2007.