

▶ Polycom® VoiceStation® 300

Crystal-clear conferencing
for smaller rooms and desktops



The quality of Polycom designed for offices and small meeting spaces

The Polycom VoiceStation 300 is a small conference phone ideally suited for desktops, offices, and other small rooms. With a microphone range of up to seven feet, the VoiceStation 300 is ideal for small conferences with three to four participants. Plus its compact industrial design fits well on a desk or small table, making it a great solution for offices. The VoiceStation 300 provides Polycom's legendary voice quality at an affordable price.

Featuring Polycom's award-winning Acoustic Clarity Technology, the VoiceStation 300 delivers significantly improved voice quality over the previous-generation VoiceStation 100. The VoiceStation 300 features three sensitive microphones that offer 360-degree room coverage. Smart technology, such as Dynamic Noise Reduction (DNR), provides maximum microphone sensitivity, while reducing distracting room and background noise. It also features technology that resists interference from mobile phones and other wireless devices, delivering clear communications with no distractions. Plus, Polycom's legendary full-duplex technology ensures that everyone on the call can be heard.

Convenient controls for volume, mute, redial, flash and hold are located on an intuitive, easy-to-use keypad. A handset phone can be plugged in for private calls, or simply switch back to the VoiceStation 300 for hands-free conversations.

Benefits

- ▶ **More productive calls** – Polycom's patented Acoustic Clarity Technology allows simultaneous, natural, free-flowing conversation
- ▶ **360-degree room coverage** – A powerful, digitally-tuned custom speaker and three sensitive microphones provide uniform coverage from up to 7 feet away
- ▶ **Hands-free calls** – A great hands-free conferencing solution for home offices and small businesses
- ▶ **Resists interference from mobile phones** – Clearer calls with no distracting noise from wireless devices
- ▶ **Easy to use and install** – Connects into any analog phone jack
- ▶ **Secondary phone options** – Plug in a fax machine or computer modem, or plug in a handset for private calls

Polycom® VoiceStation® 300 Specifications

Conference Areas

VoiceStation 300 is ideal for basic conferencing in offices and small conference rooms, accommodating 4 or fewer meeting participants

Features and Functions

VoiceStation 300 is easy-to-use, with its universal keypad and intuitive functions.

Console Size

- 9.5 in x 9.25 in x 3.0 in
- (24.2 cm x 23.5 cm x 7.6 cm) (L, W, H)

Weight

- 1.25 lbs (0.57 kg)

Power

- 110V 60Hz AC / 220V 50Hz AC (depending on country)

Network Interface

- Analog PBX or public switched telephone

Keypad

- 19-key telephone keypad including:
 - On-hook/Off-hook
 - Flash, Redial, Mute
 - Volume Up, Volume Down

LEDs

- Off-Hook
- Active Call,
- Hold
- Mute

Console Loudspeaker

- Frequency response: 300 to 3300 Hz
- Volume: Adjustable to 86 dBA SPL (peak) volume at 0.5 m

Console Microphone

- 3 cardioid microphones 300 to 3500 Hz

Audio

- Polycom Acoustic Clarity full duplex (IEEE 1329 Type 1)
- Up to 7 ft. microphone pickup range
- Gated microphones with intelligent microphone mixing
- Dynamic Noise Reduction

Regulatory Compliance

- NA CI/C-UL
- FCC Part 68
- FCC Part 15 Class B
- Canadian ICES-003
- CE Mark (R & TTE Directive)
- VCCI Class B (Japan)

Environmental Requirements

- Operating Temperature: 40 ° -104 ° F (5° to 40° C) operating
- Relative Humidity: 20% to 85% (non-condensing)
- Storage Temperature: 22°-131° F (30°-55° C)

Recommended Room Conditions

- Room Size: 225 sq. ft or 15 ft by 15 ft (<25 m² or 5m X 5m)
- Reverberation Time: <0.4 seconds
- Noise Level: <48 dBA

VoiceStation 300 Ships With

- Telephone console unit
- Power module
- 21 ft (6.4 m) cord to console
- 7 ft. (2.1 m) telco cable to RJ-11 telephone jack
- User Guide

Warranty

- 12 months

Polycom Worldwide Headquarters
4750 Willow Road, Pleasanton, CA 94588
1.800.POLYCOM or +1.925.924.6000
www.polycom.com

