



MODEL	A	B	C	D	DEPTH
PB3	4.5	2.75	.625	1.375	3
NOTE: FASTENERS NOT SHOWN ALL DIMENSIONS IN INCHES.					

PUSH BUTTON - MODEL PB3

Features

- A compact 1" x 1-3/4" push button
- 3 amp DPST contacts (field modify for DPDT)
- Back box is supplied on single gang applications
- 12-24 VDC bi-color illumination is standard
- Alternate action version available
- Narrow stile version available
- Economy non-illuminated version available
- UL Listed contacts

Operating Temperature
0 to 43C [32 to 110F]

How to Order

<u>Part #</u>	<u>Description</u>
PB3	Push Button Momentary Single Gang
PB3A	Push Button Alternate Single Gang
PB3N	Push Button Momentary Narrow Stile
PB3AN	Push Button Alternate Narrow Stile



PUSH BUTTON - MODEL PB3 (cont'd)

PB3E	Push Button Momentary Single Gang Economy
PB3EA	Push Button Alternate Single Gang Economy
PB3EN	Push Button Momentary Narrow Stile Economy
PB3EAN	Push Button Alternate Narrow Stile Economy

Architectural Specifications

- A. The Push Button shall be produced by an ISO 9001 certified manufacturer.
- B. The Push Button shall be a compact industrial grade 1" by .75" button with protective cowling.
- C. The Button shall be labeled 'EXIT" and shall be green back lit using a multi-chip LED.
- D. A separate red LED shall be provided as an additional indicator.
- E. The LED's shall operate on 12 or 24 VDC (field selectable).
- F. The switch shall be DP/ST (field modifiable to DPDT) and rated at 3 Amps at 12 or 24 VDC.
- G. The switch shall be available in momentary or alternate action, with a Stainless Steel - 630/US32D single gang face plate or narrow stile Stainless Steel - 630/US32D face plate for mullion mounting.