

# 8780

## Single-line **Caller ID\*** **Speakerphone**

*Line-Powered • NO Batteries Required!*

### FEATURES:

- **10 One-touch Speed Dial Memory Locations**
- **Mute with LCD indication**
- **Data Port** (RJ-11)
- **Message Waiting** (90V, FSK, 24V)
- **Tone/Pulse Switch**
- **Flash time** (100/200/300/600ms)
- **Hold with Music**
- **Speakerphone**
- **Pause**



**8780**

Part#878041TP227S

**CORTELCO™**



# Single-line **Caller ID<sup>\*</sup>** **Speakerphone**

# 8780

**We Listened to our customers needs!**  
**We've eliminated the need for batteries or**  
**an AC adapter to operate the telephone or to maintain**  
**Speed dial memory locations.**

**Our 8780 is our most dependable, affordable Line-Powered Telephone ever!**

## **8780 FEATURES**

### **Caller ID:**

- Multi-Angle Liquid Crystal Display
- 76 Caller ID Memories
- Supports Type I and II CID
- Multi-Language CID
- 80 Phone book entries, 16 characters for each name, 32 digits for each number
- 16 Dialed numbers review and redial
- Automatic Call Timer
- Caller ID Memories and phone book entries will be kept during power failures
- Date and Time Display
- Set Local Code
- Call Back from CID Memory
- Review Call Message
- Remove Call Message (single or all)

### **Ringer:**

- Visual Ring Indicator
- Ringer Volume 8 level adjustable
- 16 ring melodies selectable

### **Other:**

- Handset Volume 4 level adjustable
- Speaker Volume 8 level adjustable
- Desk/Wall Mountable
- Hearing Aid Compatible
- Handset Jack (2.5mm).
- Auto Busy Redial  
(up to 15 attempts to a busy number)



**CORTELCO<sup>TM</sup>**

1703 Sawyer Road  
Corinth, MS 38834  
662-287-5281  
Fax: 662-287-3889  
www.cortelco.com

Features and specifications subject to change.