




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	DIMENSIONS			WEIGHT lbs (grams) / 10 pcs
	"A"	"B"	"C"	
CRS1-125- _	1.55 (39.37)	1.43 (36.32)	1.13 (28.70)	0.247 (112.17)



NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2. PRODUCT IS MOUNTED TO APPLICATION SURFACE USING (2) CABLE TIES, UP TO A STANDARD CROSS-SECTION.
3. THIS PRODUCT CONTAINS A MALE/FEMALE ATTACHMENT SYSTEM. MAXIMUM RECOMMENDED STACK HEIGHT IS EQUAL TO 4 PARTS.
4. STANDARD CABLE TIES OR VELCRO TIES CAN BE USED TO SECURE CABLE TO THE PRODUCT.
5. PARTS ARE REVERSIBLE TO ALLOW ALTERNATING CABLE TIE TABS.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G02417BC_PB_CRS1125_00

PANDUIT CORP.

TINLEY PARK, ILLINOIS

CABLE RACK SPACER
(CRS1-125- _)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 11/26/01

FLAME RETARDANT
NYLON 6/6
25% GLASS

DRAWING NO.

GB2417BC

DWG
SIZE
A

R	11/26/01	JAD		INITIAL RELEASE	GB2417BC	R							
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP					