





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANUIT PART NO. *	DIMENSIONS				WEIGHT lbs (grams) / 10 pcs
	"A"	"B"	"C"	"D"	
CRS6- _	5.25 (133.35)	1.12 (28.55)	.800 (20.32)	.860 (21.95)	.4468 (202.7)



NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2. PRODUCT IS MOUNTED TO APPLICATION SURFACE USING (2) CABLE TIES, UP TO A STANDARD CROSS-SECTION
3. THIS PRODUCT CONTAINS A MALE/FEMALE ATTACHMENT SYSTEM WITH A LOCKING LATCH. MAXIMUM STACK HEIGHT IS EQUAL TO 5 PARTS.
4. STANDARD CABLE TIES OR VELCRO TIES CAN BE USED TO SECURE CABLE TO PART.

R	12-15-99	JAD		INITIAL RELEASE	GB2185DA	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

DIMENSIONS IN BRACKETS ARE METRIC [mm]			
CAD FILENAME/LAYERS		G02185DA_PB_CRS6_00	
 PANDUIT CORP. TINLEY PARK, ILLINOIS			
CABLE RACK SPACER (CRS6-_)			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JAD	MAT'L: POLYCARBONATE ABS BLEND	SCALE NONE	
DATE 12-15-99		DRAWING NO. GB2185DA	DWG A SIZE
CHK'D			