



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
FST24	.31 LB/EA (131.54 g/EA)

NOTES:

- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- TRAY WILL HOLD UP TO 24 MECHANICAL OR FUSION SPLICES.
- INCLUDED WITH SPLICE TRAY;
  - 1 CLEAR PLASTIC COVER.
  - 4 MECHANICAL SPLICE HOLDERS.
  - 4 FUSION HOLDERS.
  - 2 RIBBON FIBER GROMMET SLEEVES
  - 5 GREEN CABLE TIES.
  - 5 BLUE CABLE TIES.
  - 1 6" PVC TUBE.
  - 4 VELCRO SELF STICK MOUNTING PADS



COVER REMOVED FOR CLARITY

CAD FILENAME/LAYERS M00873AK\_DC\_00A.PRT

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

SPLICE TRAY UNIT  
24 MECHANICAL OR FUSION SPLICES  
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ± .010 (.3)  
(.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MAT'L:

SCALE

NONE

DATE

11-15-01

DRAWING NO.

00873-17

DWG

A

SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	11-15-01			RELEASED TO PRODUCTION.	00873-17			