

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ANTENNA KNOCKOUTS
FEATURES FOR CEILING
MOUNT APPLICATIONS.

KNOCKOUT HOLES FOR
EXTERNALLY MOUNTED
ANTENNAS.

3.06
[77.8]

13.73
[348.7]

12.00
[304.8]

KNOCKOUT CAN BE
REMOVED TO MAKE
THE LED LIGHT ON
THE WAP VISIBLE.

ANTENNA KNOCKOUTS
FEATURES FOR CEILING
MOUNT APPLICATIONS.

KNOCKOUT HOLES FOR
EXTERNALLY MOUNTED
ANTENNAS.

PANDUIT P/N

WEIGHT

PZWIFIED

4.8 LB/EACH PC
(2177.2 g/EACH PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- ENCLOSURE
 - 1- FOAM RETENSION COVER
 - 4- FIRE RESISTANT FOAM
 - 1- SLOT COVER
 - 26"- EDGE GROMMET
 - 1- CAT TX 6 PLUS JACK (CJ688TGWH)
 - 1- 2 POSITION SURFACE MOUNT BOX (CBXJ2WH-A)
 - 1- 2FT TX6 PLUS PATCH CORD (UTPSP2)
 - 1- GROUNDING WIRE WITH HARDWARE
 - 2- CABLE TIE MOUNTS (ABMM-A-C)
 - 4- PAN-TY (PLT1.5-C)
5. THE DESIGN OF THIS ENCLOSURE HAS BEEN OPTIMIZED FOR THE CISCO AIRONET[®] AP1232AG AND AP1242AG WIRELESS ACCESS POINTS.

MODEL FILENAME V10311AB_PZWIFIED_1230_03.prt

SIZE

DRAWING FILENAME V10311AB_DC_02B.prt

A

PZWIFIED PANZONE[™] WIRELESS ACCESS
POINT ENCLOSURE CUSTOMER DRAWING



PANDUIT[™]
CORP.
TINLEY PARK, ILL 60477

I.T. NUMBER N/A

PRODUCT SPEC N/A


WORK INSTRUCTION N/A

SCALE NONE

PART NO.
PZWIFIED

DRAWING NO.
10311-16
SHEET 1 OF 2

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010(.3)
(.XX) ± .031(.8) ANGLES ±



DRAWN BY
Rey B

DATE
8/17/05

CHK'D
RCD

MATERIAL:
.063" 5052 ALUMINUM

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
02	3/31/06	RYB		CAT6 PARTS REPLACE CAT5	10311-16				
01	12/9/05	RYB	RDC	A. ADDED AP1242AG ACCESS POINT	10311-16		BAS		
00	8/17/05	RYB	RDC	RELEASED TO PRODUCTION	10311-16		BAS		

