


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PRVF1596	40.0 LBS/EACH 18.2 kg/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) 8 FOOT 15" FRONT ONLY VERTICAL MANAGER (1) HARDWARE KIT (4) MOLDED FRONT SPOOLS (P/N: PRSP7)
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 8 FOOT-15" DOOR SOLD SEPARATELY (P/N: PRD1596)
- 5" REAR MOUNTING SPOOLS SOLD SEPARATELY (P/N: PRSP5)
- SPOOLS HAVE MULTIPLE MOUNTING POSITIONS TO ACCOMMODATE CABLE SLACK.
- DIMENSIONS IN PARENTHESES ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

MODEL FILENAME		V10440AE/04.PRT	
CAD FILENAME/LAYERS		V10440AE_DC/04A.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
8 FOOT VERTICAL MANAGER 15" FRONT ONLY (PRVF1596) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY BAME	MAT'L:	SCALE NONE	
DATE 6-13-07	BACKBONE- STEEL SPOOLS- POLYCARBONATE FINGERS- ABS	DRAWING NO.	DWG A SIZE
CHK'D NAGL		10440-22	

04A	1-24-11	BAME	SPK	REMOVED TOLERANCES CHANGED DOOR BRACKET DESIGN	10440-22				
01	12-14-07	BAME	NAGL	CHANGED FINGER DESIGN	10440-22		CMK		
00	6-13-07	BAME	NAGL	RELEASED TO PRODUCTION	10440-22		CMK		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH