


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

(8) BEZELS AND COVERS ARE NOT INSTALLED (PART OF KIT)




PANDUIT P/N	WEIGHT
CN4	389 LBS/EACH 176.5 Kg/EACH

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN PARENTHESES ARE METRIC [mm].
- INDEPENDENT ADJUSTABLE FRONT & REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 2.9" TO 23.9" DEPTH.
- CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
- 45 AVAILABLE RACK SPACES.
- EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS .625", .625", .500", .625", .625", .500"...ETC
- PARTS SUPPLIED:
 - 1- BASE CABINET
 - 2- SETS OF SPLIT DOORS
 - 2- SIDE PANELS
 - 1- SET OF FRONT & REAR #12-24 TAPPED RAILS
 - 1- HARDWARE KIT
 - 2- VERTICAL CABLE MANAGEMENT FINGER KITS
 - 8- BEZELS & COVERS
 - 1- INSTRUCTION SHEET
- RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
- FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
- LOAD RATING: 2500 LBS (1134 kg).
- SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.

MODEL FILENAME		V10395AZ/02.PRT
CAD FILENAME/LAYERS		V10395AZ_DC/02B.PRT
<div>PANDUIT</div> <div>CORP. TINLEY PARK, ILLINOIS</div>		
CN4 CABINET CONFIGURATION CUSTOMER DRAWING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,
INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015		[METRIC - MILLIMETER] X. +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY LEE	MAT'L:	SCALE NONE
DATE 1-31-07		DRAWING NO. 10395-58 SHEET 1 OF 4
CHK'D TKW		DWG A SIZE

02B	2-22-11	LEE	TKW	BEZELS & COVERS ADDED; SHEET 4 ADDED	10395-58		JWE		
02A	10-30-08	PIP	TKW	RELEASED TO PRODUCTION	10395-58				
00	1-31-07	LEE		DRAWING RELEASE					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



LEFT

FRONT

RIGHT

REAR

MODEL FILENAME	V10395AZ/02.PRT
CAD FILENAME/LAYERS	V10395AZ_DC/02B.PRT
PANDUIT CORP. TINLEY PARK, ILLINOIS	
CN4 CABINET CONFIGURATION CUSTOMER DRAWING	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015 [METRIC - MILLIMETER] X. +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4 ANGLE +/- 1°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
02B	2-22-11	LEE	TKW	SEE SHEET 1 OF 4 FOR REVISIONS	10395-58		JDWE			DRAWN BY LEE	SCALE NONE DRAWING NO. 10395-58 SHEET 2 OF 4 DWG A SIZE
02A	10-30-08	PIP	TKW	SEE SHEET 1 OF 3 FOR REVISIONS	10395-58					DATE 1-31-07	
00	1-31-07	LEE		SEE SHEET 1 OF 3 FOR REVISIONS	10395-58					CHK'D TKW	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

REMOVABLE
ACCESS COVER
FOR 12" X 12"
OPENING


(4) #12-24 TAPPED
EQUIPMENT RAILS
ADJUSTABLE FROM
2.9" TO 23.9" DEPTH

RACK UNITS ARE
NUMBERED AND
INDEXED FOR
IDENTIFICATION

VERTICAL
CABLE
MANAGEMENT
FINGERS WITH
BEND RADIUS
CONTROL

CROSS BEAMS ARE
MARKED EVERY 1/2"
FOR EQUIPMENT RAIL
ALIGNMENT


SPLIT DOOR & SIDE PANELS
NOT SHOWN




MODEL FILENAME	V10395AZ/02.PRT
CAD FILENAME/LAYERS	V10395AZ_DC/02B.PRT
PANDUIT CORP. TINLEY PARK, ILLINOIS	
CN4 CABINET CONFIGURATION CUSTOMER DRAWING	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015 [METRIC - MILLIMETER] X. +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4 ANGLE +/- 1°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
02B	2-22-11	LEE	TKW	SEE SHEET 1 OF 4 FOR REVISIONS	10395-58		JONE			DRAWN BY LEE	SCALE NONE
02A	10-30-08	PIP	TKW	SEE SHEET 1 OF 3 FOR REVISIONS	10395-58					DATE 1-31-07	DRAWING NO. 10395-58 SHEET 3 OF 4
00	1-31-07	LEE		SEE SHEET 1 OF 3 FOR REVISIONS	10395-58					CHK'D TKW	DWG A SIZE

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT OF CABINET



DETAIL A
SCALE 1:4

MODEL FILENAME	V10395AZ/02.PRT
CAD FILENAME/LAYERS	V10395AZ_DC/02B.PRT
PANDUIT CORP. TINLEY PARK, ILLINOIS	
CN4 CABINET CONFIGURATION CUSTOMER DRAWING	

										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015 [METRIC - MILLIMETER] X. +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4 ANGLE +/- 1°			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
02B	2-22-11	LEE	TKW	SEE SHEET 1 OF 4 FOR REVISIONS	10395-58		JDWE					DRAWN BY LEE DATE 1-31-07 CHK'D TKW	MAT'L:	SCALE NONE	
02A	10-30-08	PIP	TKW	SEE SHEET 1 OF 3 FOR REVISIONS	10395-58									DRAWING NO. 10395-58 SHEET 4 OF 4	DWG A SIZE
00	1-31-07	LEE		SEE SHEET 1 OF 3 FOR REVISIONS	10395-58										
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH					