




NOTES:
1. SEE MFG. DRAWING NO. A61208.
2. MILLIMETER ARE IN [].

PART NO.				MATERIAL	MARKER SIZE	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.		CAD FILENAME/LAYERS			
C100X025YJJ				GMV54W-1J	1.00 X 0.250	210	48	10000		I00472GN_C10245_C100X025YJJ_00.prt			
										PANDUIT CORP TINLEY PARK, ILLINOIS OPTIMUM C100X025YJJ LASER/INKJET LABELS			
2	5/2/07	RVU		ADDED "INKJET" ON HEADER.			4971	R		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (,XXX) ± .005 (.XX) ± .015 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
1	4-23-04	RVU	DWY	LABELS WERE BUTT-CUT.			3599	R		DRAWN BY RVU	SEE TABLE	SCALE NTS	
0	9-29-04	RVU	DWY	RELEASED TO PRODUCTION.			3543	R		DATE 9-29-04		DRAWING NO. C10245	DWG B
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP	CHK'D DWY	SIZE