


PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.	COLOR
C100X050KBT	GMK4	1.00 [25.40] X X 0.50 [12.70]	3	10,000	WHITE
C100X050YJT	GMY2				WHITE
C100X050CBT	GMC4				WHITE
C100X050AAT	GMY4STE				SILVER
C100X050FNT	GMPE4-W				WHITE
C100X050PBT	GMP4-W				WHITE
C100X050YMT	GMY4-S				SILVER
C100X050TJT	GMT4-W				WHITE
C100X050YPT	GMY4-HTW				WHITE



NOTES:
1. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS		100472EJ-DC-C10266/08H	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING		OPTIMUM C100X050**T	
THERMAL TRANSFER LABELS			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU		SCALE NTS	
DATE 9-30-04		SEE TABLE	
CHK		DRAWING NO. C10266	
		DWG A SIZE	

7	10/5/11	RVU	ADD NEW PN: C100X050YPT. UPDATE TOL.	6528	R				
6	9/14/10	RVU	REMOVED C100X050YKT FROM THE TABLE.	6126	R				
5	10/24/08	RVU	GMY4-C WAS GMY4-HTC. TOL. INCORRECT.	5582	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	