


PART NO.	MATERIAL	COLOR	MARKER SIZE	LABELS PER SHEET	SHEET PER PKG.	STANDARD PKG. QTY.
C100X050YJJ	GMY	WHITE	1.00 X 0.500	119	85	10000
C100X050YLJ	GMY	SAFETY YELLOW	1.00 X 0.500	119	43	5000
C100X050YMJ	GMY	SILVER	1.00 X 0.500	119	43	5000
C100X050YOJ	GMY	SILVER	1.00 X 0.500	119	43	5000



NOTES:
1. SEE MFG. DRAWING NO. A61209.
2. MILLIMETER ARE IN [].

										PANDUIT CORP TINLEY PARK, ILLINOIS			
										OPTIMUM C100X050Y*J LASER/INKJET LABELS			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
I	5/2/07	RVU		ADDED "INKJET" ON HEADER.	4971	R				DRAWN BY RVU	MATT'L : SEE TABLE	SCALE NTS	
O	9-30-04	RVU		DRAWING RELEASED.	0000	R				DATE 9-30-04		DRAWING NO. C10246	DWG B SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D			