


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C200X050YJJ	GMV	2.000 [50.8] X 0.500 [12.7]	64	16	1000

NOTES:

1. SEE MFG. DRAWING NO. A61217.
2. MILLIMETER ARE IN [].

CAG FILENAME/LAYERS 1004726Y_C10254_C200X050YJJ_00.PRT									
PANDUIT CORP TINLEY PARK, ILLINOIS									
OPTIMUM C200X050YJJ LASER/INKJET LABELS									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ±					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION				
DRAWN BY RVU					MAT'L:		SCALE NTS		
DATE 9-30-04					SEE TABLE		DRAWING NO. C10254		DRG SIZE B
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP
0	9-30-04	RVU		DRAWING RELEASED.	0000		R		