


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER		MATERIAL		MARKER SIZE inches [mm]		LABELS PER SHEET		SHEET QTY.		STANDARD PKG. QTY.	
S050X150YAJ		GMY6 CLEAR POLYESTER FILM		0.500 [12.7] X X 1.500 [38.1]		78		65		5000	
										CAD FILENAME/LAYERS I00472CB_DC_C10202/02C	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										CUSTOMER DRAWING OPTIMUMM SELF-LAM. LASER INKJET PRINTABLE LABELS	
2	10/29/09	RVU		UPDATE ON TOLERANCES. ADD +/- .062.				5898	R		
1	8/12/08	RVU		CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.				5516	R		
0	6-29-06	RVU		DRAWING RELEASE. MAT'L WAS GMY2.				4568	R		
A	9-22-04	RVU		ENGRG. RELEASE.				0000	R		
REV	DATE	BY	CHK	DESCRIPTION				ECN	- R	CUST	SUP
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										SCALE NTS	
										DRAWING NO. C10202	
										DWG A SIZE	
										DRAWN BY RVU	
										DATE 9/22/04	
										CHK'D	
										MAT'L; SEE TABLE	