


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	COLOR (PMS)	LABELS SHEET	SHEET QTY.	STD. PKG. QTY.		
S100X150YAJ	GMY6 CLEAR POLYESTER FILM	1.000 (25.4) X 1.500 (38.1)	WHITE	42	60	2500		
S100X150YBJ			BLUE (291C)					
S100X150YCJ			BROWN (465C)					
S100X150YDJ			GREEN (353C)					
S100X150YEJ			GRAY (422C)					
S100X150YFJ			ORANGE (150C)					
S100X150YGJ			PURPLE (264C)					
S100X150YHJ			RED (184C)					
S100X150YIJ			YELLOW (101C)					
S100X150YAJ-D			WHITE				12	500
S100X150YBJ-D			BLUE (291C)					
S100X150YDJ-D			GREEN (353C)					
S100X150YHJ-D	RED (184C)							
S100X150YIJ-D	YELLOW (101C)							

CAD FILENAME/LAYERS 100472CE_DC_C10205/04E

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
4	10/29/09	RVU		UPDATE ON TOLERANCES. ADD +/- .062.	5898	R		
3	8/12/08	RVU		CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.	5516	R		
2	8/13/07	RVU		ADDED NEW P/N, C100X150YCJ, C100X150YEJ, C100X150YFJ AND C100X150YGJ.	5016	R		
1	9-12-06	RVU		ADDED PART NUMBER WITH -D.	4680	R		
0	6-29-06	RVU		DRAWING RELEASE. MAT'L WAS GMY2.	4568	R		
A	9-22-04	RVU		ENGRG. RELEASE.	0000	R		

PANDUIT

CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING OPTIMUMM SELF-LAM.
LASER INKJET PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) ± .12 (.XXX) ± .025
 (.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: RVU
 DATE: 9/22/04
 CHK'D:

MAT'L: SEE TABLE

SCALE: NTS

DRAWING NO. C10205
 DWG. SIZE: A