


TABLE 1				
PART NO.	MATERIAL	WRITE-ON AREA	LABELS PER SHEET	SHEETS PER BOOK
PSCB-12	GMV3	WHITE	18	10
PSCB-12Y	GMV3	WHITE	18	10



NOTES:
 1. SEE MFG. DWG. NO. A60325.
 2. DIMENSION IN [] ARE IN MILLIMETERS.

										CAD FILENAME/LAYERS		100618CM_C10369_PSCB_00.PRT		
										<h1>PANDUIT</h1> CORP TINLEY PARK, ILLINOIS CUSTOMER DRAWING PSCB-12, PSCB-12Y SELF-LAM. 0.50" X 1.50" LABEL				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .010 (.XX) ± .015 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION		
O	6-8-06	RVU		RELEASE TO PRODUCTION.	4542	R				DRAWN BY	RVU	MAT'L:	SCALE	3/4
A	8-18-05	RVU		ENGINEERING RELEASE	0000	R				DATE	8-18-05	SEE TABLE 1	DRAWING NO.	C10369
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D			DWG	B
													SIZE	