



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	"A" ±.062	MARKER ACROSS	TUBING COLOR
H100X084H1T	A	1.00 [25.40]	2	WHITE
H200X084H1T	B	2.00 [50.80]	1	
H100X084H2T	A	1.00 [25.40]	2	YELLOW
H200X084H2T	B	2.00 [50.80]	1	
H100X084H3T	A	1.00 [25.40]	2	BLACK
H200X084H3T	B	2.00 [50.80]	1	
H100X084H4T	A	1.00 [25.40]	2	RED
H200X084H4T	B	2.00 [50.80]	1	



NOTE:
1. DIMENSIONS IN () ARE IN MILLIMETERS.

CAD FILENAME/LAYERS 100923NK-DC-C10436/09J

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING H***X084H** OPTIMUM
COMPUTER PRINTABLE MIL. SPEC.
HEAT SHRINK MARKERS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
8	4/12/12	RVU	<i>ML</i>	REVISED ON DETAIL A, B, DESIGN TO SHOW ALL MARKERS.	6731	R		
7	12/1/10	RVU		Change box design	6230	R		
6	5/21/09	RVU		+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010, HT: .84 +/- .062 WAS .840. MAT'L: HSK TUBING GMUHS31, 3.5 WIDE LINER WAS GMUHS. ADD "A" +/- .062.	5593	R		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± 0.12 (.XXX) ± .020 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU	MAT'L: HEATSHRINK TUBING GMUHS31, 3.5 WIDE LINER	SCALE NTS	
DATE 8-2-06		DRAWING NO. C10436	DWG A SIZE
CHK'D <i>ML</i>			