



PART NO.	MATERIAL	COLOR	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C200X100YJJ	GMY	WHITE	2.000 [50.8] X 1.000 [25.4]	36	28	1000
C200X100YLJ	GMY	SAFETY YELLOW	2.000 [50.8] X 1.000 [25.4]	36	28	1000
C200X100YMJ	GMY	SILVER	2.000 [50.8] X 1.000 [25.4]	36	28	1000

NOTES:
 1. SEE MFG. DRAWING NO. A61218.
 2. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS I00472GZ_C10255_C200X100YxJ_00.PRT

						PANDUIT CORP. TINLEY PARK, ILLINOIS	
						OPTIMUM C200X100Y*J LASER/INJET LABELS	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (,XXX) ± .005 (.XX) ± .015 ANGLES ±	
						UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
1	5/2/07	RVU		ADDED "INKJET" ON HEADER.	4971	R	
0	9-30-04	RVU		DRAWING RELEASED.	0000	R	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST SUP
						DRAWN BY: RVU MAT'L: SEE TABLE	
						DATE: 9-30-04	
						SCALE: NTS	
						DRAWING NO. C10255 DWG SIZE B	