


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.
C150X075YMT	GM4-S	1.500" [38.1] X X	1	5000
C150X075PBT	GMP4-W			
C150X075CBT	GMC4	0.750" [19.05]		
C150X075YJT	GM4-W			

NOTES:  
 1. SEE MFG. DRAWING NO. A61230.  
 2. MILLIMETER ARE IN [ ].

CAD FILENAME/LAYERS  
 100472HK\_C10267\_C150X075YJT\_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
 OPTIMUM C150X075\*\*T  
 THERMAL TRANSFER LABELS

UNLESS OTHERWISE SPECIFIED,  
 DIMENSIONAL TOLERANCES ARE:  
 (.X) ± .031 (.XXX) ± .005  
 (.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
 ALL DIMENSIONS ARE GIVEN  
 IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
 RVU

MAT'L:

SCALE  
 NTS

DATE  
 9-30-04

SEE TABLE

DRAWING NO.

C10267

DWG  
 A  
 SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	9-30-04	RVU		DRAWING RELEASE.	4992	R		