


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [ each ]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA11-A THRU PCA11-Z	'A' THRU 'Z'	30	300	1	10	.110" - .130"
PCA11-A-J	'A' - 'J' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-K-T	'K' - 'T' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-U-Z	'U' - 'Z' [ 1 EA. ] '-' [ 2 EA. ] '+' [ 2 EA. ]	30	300	1	10	.110" - .130"
PCA11-0 THRU PCA11-9	'0' THRU '9'	30	300	1	10	.110" - .130"
PCA11-0-9	'0' - '9' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-MIN	'-'	30	300	1	10	.110" - .130"
PCA11-PLS	'+'	30	300	1	10	.110" - .130"

4

4

NOTES:  
1. COLOR: WHITE WITH BLACK LEGENDS.  
2. MILLIMETERS ARE IN [ ].



CAD FILENAME/LAYERS		100281DB-DC-C10351/04D	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING PCA11-* CLIP-ON WIRE MARKER			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± .062		(.XXX) ± .015	
(.XX) ± .031		ANGLES ±	
DRAWN BY	RVU	MAT'L:	SCALE
DATE	10-14-04	WHITE MARKER - ACETAL	DRAWING NO.
CHK'D			C10351
ECN	R	CUST	DWG SIZE
SUP			A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	3/28/11	RVU		ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [ 1 EA. ].	6336	R		
2	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R		
1	10-06-06	RVU		ADDED TOLERANCE AND REVISED TABLE.	4881	R		
0	9-12-06	RVU		DRAWING RELEASE	3732	R		