


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA18-A THRU PCA18-Z	'A' THRU 'Z'	30	300	1	10	.185" - .234"
PCA18-A-J	'A' - 'J' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-K-T	'K' - 'T' [1 EA.]	30	300	1	10	.185" - .234"
4 PCA18-U-Z	'U' - 'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.185" - .234"
PCA18-0 THRU PCA18-9	'0' THRU '9'	30	300	1	10	.185" - .234"
4 PCA18-0-9	'0' - '9' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-MIN	'-'	30	300	1	10	.185" - .234"
PCA18-PLS	'+'	30	300	1	10	.185" - .234"

NOTES:

- COLOR: WHITE WITH BLACK LEGENDS.
- MILLIMETERS ARE IN [].



SYMBOLS ARE LOCATED ON BOTH SIDE OF MARKERS.

CAD FILENAME/LAYERS 100281DC-DC-C10396/04D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PCA18-* CLIP-ON WIRE MARKER

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	3/28/11	RVU		ADD '-' 2 EA. AND '+' 2 EA. '0'-'9'. 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336	R		
2	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R		
1	10-06-06	RVU		ADDED TOLERANCE AND REVISED TABLE.	4881	R		
0	9-12-06	RVU		DRAWING RELEASE	3732	R		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .062 (.XXX) ± .015 (.XX) ± .031 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU	MAT'L: WHITE MARKER -ACETAL	SCALE	
DATE 10-14-04	CHK'D	DRAWING NO. C10396	DWG SIZE A