


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA07-A THRU PCA07-Z	'A' THRU 'Z'	30	300	1	10	.08" - .10"
PCA07-A-J	'A'-'J' [1 EA.]	30	300	1	10	.08" - .10"
PCA07-K-T	'K'-'T' [1 EA.]	30	300	1	10	.08" - .10"
4 PCA07-U-Z	'U'-'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.08" - .10"
PCA07-0 THRU PCA07-9	'0' THRU '9'	30	300	1	10	.08" - .10"
4 PCA07-0-9	'0'-'9' [1 EA.]	30	300	1	10	.08" - .10"
PCA07-MIN	'-'	30	300	1	10	.08" - .10"
PCA07-PLS	'+'	30	300	1	10	.08" - .10"

NOTES:
 1. COLOR: WHITE WITH BLACK LEGENDS.
 2. MILLIMETERS ARE IN [].



CAD FILENAME/LAYERS		100281DA-DC-C10510/04D	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING PCA07-* CLIP-ON WIRE MARKER			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .062 (.XXX) ± .015 (.XX) ± .031 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU	MAT'L:	SCALE	
DATE 9-16-96	WHITE MARKER -ACETAL	DRAWING NO. C10510	DWG SIZE A
CHK'D			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
4	3/28/11	RVU		ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.]	6336	R		
3	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R		
2	2-15-07	RVU		ADD TOL. AND NOTES 1 THRU 5. ADD P/N.	4882	R		
1	10-06-06	RVU		REMOVED "PMW" ON ALL PART NUMBERS.	4716	R		
0	9-12-06	RVU		DRAWING RELEASE	4677	R		