


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART<br>NUMBER | LEGEND                                                     |                                         | COLORS  |            | WIDTH       | LENGTH<br>+15%/-5% | STD.<br>PKG. | LEGEND<br>HEIGHT "A" |
|----------------|------------------------------------------------------------|-----------------------------------------|---------|------------|-------------|--------------------|--------------|----------------------|
|                | OPTION 1                                                   | OPTION 2                                | LEGENDS | BACKGROUND |             |                    |              |                      |
| HTDU2R-E       | CAUTION CAUTION CAUTION<br>ELECTRIC LINE BURIED BELOW      | CAUTION ELECTRIC LINE BURIED BELOW      | BLACK   | RED        | 2" +/- .145 | 1000 FT.           | 1 ROLL       | 1" +/- .375          |
| HTDU3R-E       |                                                            |                                         |         |            | 3" +/- .17  |                    |              | 2" +/- .375          |
| HTDU6R-E       |                                                            |                                         |         |            | 6" +/- .27  |                    |              | 4.25" +/- .75        |
| HTDU20-FO      | CAUTION CAUTION CAUTION<br>FIBER OPTIC CABLE BURIED BELOW  | CAUTION FIBER OPTIC CABLE BURIED BELOW  |         | ORANGE     | 2" +/- .145 |                    |              | 1" +/- .375          |
| HTDU30-FO      |                                                            |                                         |         |            | 3" +/- .17  |                    |              | 2" +/- .375          |
| HTDU60-FO      |                                                            |                                         |         |            | 6" +/- .27  |                    |              | 4.25" +/- .75        |
| HTDU3R-HE      | CAUTION CAUTION CAUTION<br>HIGH VOLTAGE CABLE BURIED BELOW | CAUTION HIGH VOLTAGE CABLE BURIED BELOW |         | RED        | 3" +/- .17  |                    |              | 2" +/- .375          |
| HTDU3G-S       | CAUTION CAUTION CAUTION<br>SEWER LINE BURIED BELOW         | CAUTION SEWER LINE BURIED BELOW         |         | GREEN      | 3" +/- .17  |                    |              | 2" +/- .375          |
| HTDU20-T       | CAUTION CAUTION CAUTION<br>TELEPHONE LINE BURIED BELOW     | CAUTION TELEPHONE LINE BURIED BELOW     |         | ORANGE     | 2" +/- .145 |                    |              | 1" +/- .375          |
| HTDU30-T       |                                                            |                                         |         |            | 3" +/- .17  |                    |              | 2" +/- .375          |
| HTDU60-T       |                                                            |                                         |         |            | 6" +/- .27  |                    |              | 4.25" +/- .75        |
| HTDU2B-W       | CAUTION CAUTION CAUTION<br>WATER LINE BURIED BELOW         | CAUTION WATER LINE BURIED BELOW         |         | BLUE       | 2" +/- .145 |                    |              | 1" +/- .375          |
| HTDU3B-W       |                                                            |                                         |         |            | 3" +/- .17  |                    |              | 2" +/- .375          |



NOTES:

1. MATERIAL: .35 MIL SOLID ALUMINUM CORE ENCASED IN A PROTECTIVE PLASTIC JACKET. TOTAL THICKNESS 4.0-8.5 mils.
2. MATERIAL IS NOT BIODEGRADABLE.
3. LETTER STYLE TO BE HELVETICA BOLD.
4. LEGENDS OPTION 1 OR OPTION 11 ARE ACCEPTABLE.

|                                                  |          |     |     |                                                                                                 |  |      |   |      |     |                                                                                                                 |  |                                                                                               |  |          |
|--------------------------------------------------|----------|-----|-----|-------------------------------------------------------------------------------------------------|--|------|---|------|-----|-----------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------|--|----------|
| 4. LEGENDS OPTION 1 OR OPTION 11 ARE ACCEPTABLE. |          |     |     |                                                                                                 |  |      |   |      |     | CAD FILENAME/LAYERS<br>100318HJ-DC-C10627/13J                                                                   |  |                                                                                               |  |          |
|                                                  |          |     |     |                                                                                                 |  |      |   |      |     | PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                             |  |                                                                                               |  |          |
| 6                                                | 3/12/12  | RVU |     | ADD HTDU3R-HE ON TABLE.<br>SEQUENCE PART LISTED.                                                |  | 6732 | R |      |     | CUSTOMER DRAWING<br>HTDU UNDERGROUND DETECTABLE TAPE                                                            |  |                                                                                               |  |          |
| 5                                                | 9/27/11  | RVU |     | MISSPELL-CAUTION SHOULD BE CAUTION.<br>(SEE NOTES 6) REMOVED. 4.0-8.5 MILS WAS<br>4.5-6.0 MILS. |  | 6523 | R |      |     |                                                                                                                 |  |                                                                                               |  |          |
| 4                                                | 8/4/11   | RVU |     | ADD NEW PN: HTDU3G-S AND HTDU3B-W.<br>UPDATE THE LEGEND HEIGHT SIZES. & TOL.                    |  | 6449 | R |      |     |                                                                                                                 |  |                                                                                               |  |          |
| 3                                                | 6/14/11  | RVU |     | VOID.                                                                                           |  | 6431 | R |      |     | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± .25 (.XXX) ± .045<br>(.XX) ± .145 ANGLES ± |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |  |          |
| 2                                                | 2/22/11  | RVU |     | ALL LEGENDS ON OPTION 1 AND 2 AREN'T<br>MATCH. ALL INCORRECT.                                   |  | 6311 | R |      |     | DRAWN BY<br>RVU<br>DATE<br>10/29/07<br>CHK'D <i>RVU</i>                                                         |  | SCALE<br>NTS                                                                                  |  |          |
| 1                                                | 12/16/09 | RVU |     | 4.5 mils to 6.0 mils was 5.5 mils.<br>UPDATE TOLERANCES.                                        |  | 5931 | R |      |     |                                                                                                                 |  | DRAWING NO.<br>C10627                                                                         |  | DWG<br>A |
| 0                                                | 10/29/07 | RVU |     | DRAWING RELEASE                                                                                 |  | 5193 | R |      |     |                                                                                                                 |  | SEE NOTE 1.                                                                                   |  | SIZE     |
| REV                                              | DATE     | BY  | CHK | DESCRIPTION                                                                                     |  | ECN  | R | CUST | SUP |                                                                                                                 |  |                                                                                               |  |          |