


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	LEGEND	COLORS		WIDTH NOTE (3)	LENGTH (3)	STD. PKG.	MINIMUM LEGEND HEIGHT	PART # HEIGHT
		LEGEND	BACKGROUND					
HTU30-F0-M	CAUTION CAUTION CAUTION FIBER OPTIC CABLE BURIED BELOW	BLACK	ORANGE	3"	1000 FT.	1 ROLL	3/4"	3/16"
HTU60-F0				6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU60-TV	CAUTION CAUTION CAUTION CABLE TV LINE BURIED BELOW	BLACK	ORANGE	6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU3Y-E-M	 CAUTION CAUTION CAUTION ELECTRIC LINE BURIED BELOW	BLACK	YELLOW	3"	1000 FT.	1 ROLL	3/4"	3/16"
HTU6Y-E				6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU3R-E-M	 CAUTION CAUTION CAUTION ELECTRIC LINE BURIED BELOW	BLACK	RED	3"	1000 FT.	1 ROLL	3/4"	3/16"
HTU6R-E				6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU6Y-G	CAUTION CAUTION CAUTION GAS LINE BURIED BELOW	BLACK	YELLOW	6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU3G-T-M	CAUTION CAUTION CAUTION TELEPHONE LINE BURIED BELOW	BLACK	GREEN	3"	1000 FT.	1 ROLL	3/4"	3/16"
HTU30-T-M	CAUTION CAUTION CAUTION TELEPHONE LINE BURIED BELOW	BLACK	ORANGE	3"	1000 FT.	1 ROLL	3/4"	3/16"
HTU60-T				6"	1000 FT.	1 ROLL	1 15/16"	3/16"
HTU3Y-EF-M	 CAUTION CAUTION CAUTION ELECTRIC LINE BURIED BELOW	BLACK	YELLOW	3"	1000 FT.	1 ROLL	3/4"	3/16"
	ATTENTION ATTENTION ATTENTION LIGNE ELECTRIQUE ENFOUIE							

NOTES:

- 1) MATERIAL IS 4.0 MIL +/-1.0.
THICK LOW DENSITY POLYETHYLENE.
- 2) MATERIAL IS NOT BIODEGRADABLE.
- 3) TOLERANCES:
WIDTH: 3" - +/- .20
6" - +/- .40
LENGTH: +15%, -5%
- 4) ALL COLORS ARE APWA RECOMMENDED.
- 5) REPEAT FOR HTU3Y-EF-M IS 65".

LEGEND SHOWN FOR REFERENCE ONLY.
SEE TABLE FOR ALL AVAILABLE LEGENDS
AND LEGEND OPTIONS. LEGENDS TO BE
CENTERED ON TAPE WIDTH.



										CAD FILENAME/LAYERS		100278AL_DC_C10746/15H	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										PANDUIT UNDERGROUND TAPE			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± SEE NOTE 3 (.XXX) ± SEE NOTE 3 (.XX) ± SEE NOTE 3 ANGLES ± 1°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
7	7/13/11	RVU		HTU3Y-E-M, HTU3Y-EF-M and HTU6Y-E should be "ELECTRIC" not "ELECTRICAL".		6458	R			DRAWN BY	JJM	MAT'L:	
6	3/5/09	RVU		ADD (3) ON COLUMN OF "LENGTH".		5694	R			DATE	5-22-91	GMPE2- 4.0 MIL LOW DENSITY POLYETHYLENE	
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	CHK'D		SCALE	
												1 : 2	
												DRAWING NO.	
												C10746	
												DWG	
												A	
												SIZE	