


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- ▲ 4
- ▲ 4
- ▲ 4
- ▲ 4
- ▲ 4

PART NO.	COLOR	MATERIAL	QTY.
M300X100Y6T	YELLOW	GMY/GMPO	500
M300X100Y7T	WHITE	GMY/GMPO	500
M300X100A1T	RED	GMY/GMPO	500
M300X100AGT	ORANGE	GMY/GMPO	500
M300X100AFT	GRAY	GMY/GMPO	500
M300X100ACT	BLUE	GMY/GMPO	500
M300X100AET	GREEN	GMY/GMPO	500

NOTES:
1. DIMENSIONS IN [] ARE IN MILLIMETERS.

CAD FILENAME/LAYERS 100472KO_DC_C10421/03E

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
THERMAL TRANSFER MARKER PLATE
M300X100Y*T AND M300X100A*T

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .020
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU

MAT'L:

SCALE NTS

DATE 3-15-06

SEE TABLE

DRAWING NO.

C10421

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
4	3/10/09	RVU		ADD NEW COLOR PARTS: M300X100A1T, M300X100AGT, M300X100AFT, M300X100ACT, & M300X100AET.	5678	R		
3	1/28/09	RVU		+/- .12, +/- .062 AND +/- .020 WAS +/- .1, +/- .050, AND +/- .025. CHANGED FORMAT B TO A SIZE.	5650	R		
2	10/3/08	RVU		ECN 5561 WAS CANCELLED.	5561	R		
1	4/21/08	RVU		INCREASE +/- .050 AND +/- .025 ON TITLE AREA. REMOVED "MARKER PLATE VIEW", FIG. 1. AND NOTES 1.	5399	R		
0	5-26-06	RVU		RELEASED TO PRODUCTION.	4522	R		