



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PRODUCT WORKS WITH PANDUIT PART NUMBERS:	APPLICATION SURFACE:	WEIGHT lbs / 10 (g) / pcs.
JMTRB38-1--	JMJH2 JMOD CABLE SUPPORT JMCB JMOD CHAINING BRACKET	1/4" or 3/8" THREADED ROD	2.57 (1166)



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER DESIGNATION, PACKAGE SIZE OPTIONS AND COLOR.
2. TWO NUTS APPROPRIATE FOR THE THREADED ROD USED ARE REQUIRED TO COMPLETE A RIGID INSTALLATION.
3. ASSEMBLY COMPONENT MATERIALS:
A. PRE-GLAVANIZED STEEL (JMCM25-1)
B. ZINC PLATED STEEL (RIVET)
C. SPRING STEEL (THREADED ROD BRACKET)
4. RATED STATIC LOAD: 180 lbs. (81.65kg)
5. JMTRB38-1 WILL ACCEPT TWO MJH2 J HOOK PRODUCTS.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G02672DP_PS_JMTRB381_00

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

JMOD THREADED ROD
BRACKET ASSEMBLY
(JMTRB38-1--)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE

NONE

DATE
3/7/03

SEE NOTE 3

DRAWING NO.

GB2672DP

DWG
SIZE
A

R	3/7/03	JAD		INITIAL RELEASE	GB2722DP	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		