


NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

PANDUIT* PART NO.	USE WITH THESE CABLE TIE ** CROSS SECTIONS	WEIGHT lbs / 100 pcs. (g)
ABM4H-AT	M, I, S, LH & H	1.08 (492)




ADHESIVE TAPE: PRESSURE SENSITIVE FOAM
0.040(1.01) THICK WITH ACRYLIC ADHESIVE AND
PROTECTIVE LINER. MOUNT IS DESIGNED TO
SUPPORT 2.0 lbs.(907g) MAX. WEIGHT ON A
CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
- 2) CABLE TIE CROSS SECTION CODE: M=MINIATURE, I=INTERMEDIATE, S=STANDARD, LH=LIGHT HEAVY, H=HEAVY. MOUNT SHOULD NOT BE USED WITH M, I OR S CROSS SECTION CABLE TIES WITH LESS THAN A 2" BUNDLE DIAMETER.
- 3) MOUNT HAS CONTINUOUS OPERATEING TEMPERATURE OF 180°F (82°C).

TO APPLY MOUNT

- 1) REMOVE MOUNT FROM PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION.
- 3) APPLY PRESSURE TO MOUNT.



(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G00239GT_DC_01



CORP.

TINLEY PARK, ILLINOIS

ABM4H-AT
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
(.XX) ± 0.05 (1.3) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
CGSM

MAT'L:

DATE	10-6-00
------	---------

WHITE
NYLON 6/6

SCALE	FULL
-------	------

DRAWING NO.

GB0239GT

DWG
A
SIZE

I	10-30-00	CGSM		CHANGED DIMS TO REF, CHANGED APPLICATION NOTE 1, ADDED NOTE 3, REMOVED DIM.	GB0239GT	I				
R	10-6-00	CGSM		INITIAL RELEASE	GB0239GT	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			