



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER *	COLOR	USE WITH THESE CABLE TIE ** CROSS-SECTIONS	WEIGHT LBS (g)/100 pcs
EMS - A	Ⓐ NATURAL	M, I, S	0.55 (250)
EMS - A - O	WEATHER RESISTANT BLACK	M, I, S	0.55 (250)

NOTES:

1. DESIGNED FOR USE WITH EPOXY ADHESIVE
(ADHESIVE NOT INCLUDED WITH EMS-A)
2. MOUNTING INSTRUCTIONS:
 - (A) APPLY ADHESIVE TO PART.
 - (B) APPLY SUFFICIENT PRESSURE TO FORCE
ADHESIVE INTO GROOVES.
 - (C) ALLOW ADHESIVE TO CURE BEFORE APPLYING
LOAD TO MOUNT.
3. FOR PACKAGE SIZE SEE PART NUMBER
SUFFIX DESIGNATION ON CURRENT PRICE
SHEET.
4. CABLE TIE CROSS-SECTION CODE:
M=MINIATURE, I=INTERMEDIATE,
S=STANDARD.



DIMENSIONS IN PARENTHESES ARE IN METRIC.

G00239HZ_P1_EMS_01

CORP.

TINLEY PARK, ILLINOIS

EMS - A
EPOXY MOUNT, STANDARD

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

MAT'Ls

NYLON 6/6

DRAWING NO.

**DOD
A
SIZE**

1	6/26/03	LGG		CHG DIM FROM 0.210=0.015/-0.005 TO +/- .015. CHG DIM FROM (5.3+0.38/0.13 TO +/- .38.	GB0239HZ	I			
				CHG DIM FROM 0.065+0.015/-0.005 TO -.010 CHG DIM FROM(1.7+0.38/-0.13 TO -.25					
R	6/22/01	LGG		INITIAL RELEASE REPLACED SS-4810	GB0239HZ	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

DIMENSIONS IN PARENTHESES ARE IN METRIC.				
C/D FILENAME/LAYER		G00239HZ_PI_EMS_01		
PANDUIT CORP. TINLEY PARK, ILLINOIS				
EMS-A EPOXY MOUNT, STANDARD				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± XX (.XXX) ± 0.02 (.XX) ± 0.02 ANGLES ± XX		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
DRAWN BY LGG	MAT'L: NYLON 6/6		SCALE NONE	
DATE 6/22/01			DRAWING NO. GB0239HZ	C/D A
CHK'D				SIZE