



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	A ±.030 ±(.762)	B	C	WEIGHT lbs./100 (g) / pcs.
MP150	1.50 (38.1)	1.03 (26.2)	1.69 (42.9)	0.07 (30)
MP175	1.75 (44.4)	1.28 (32.5)	1.94 (49.3)	0.08 (36)
MP200	2.00 (50.8)	1.53 (38.9)	2.19 (55.6)	0.09 (30)
MP250	2.50 (63.5)	2.03 (51.6)	2.69 (68.3)	0.12 (55)
MP350	3.50 (88.9)	3.03 (77.7)	—	0.16 (75)



**NOTES:**

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- USE WITH ANY OF THESE TIES:  
M=MINIATURE  
I=INTERMEDIATE  
S=STANDARD
- PART NO. & WEIGHT SHOWN SPECIFIES INDIVIDUAL PIECES, ADD SUFFIX "-R" TO PART NO. TO SPECIFY CONTINUOUS ROLLS OF 1000 PIECES. PART NO. MP350 IS NOT AVAILABLE IN ROLLS.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS G00239GM\_PB\_MRKRPLTE\_01

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

**IDENTIFICATION MARKER PLATE**

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	10-22-01	LGG		TOOK OF +/- REF FROM 'B' & 'C' DUE TO ADDED 'REF' ON REV 2	G80239GM	2		
1	8/14/01	LGG		ADDED REF & UPDATED	G80239GM	1		
R	1-10-00	JAD		INITIAL RELEASE, REPLACES SS-4551 REV 5	G80239GM	R		

DRAWN BY JAD  
DATE 1/10/2000  
CHK'D

MAT'L: WHITE NYLON

SCALE NONE  
DRAWING NO. G80239GM  
DWG SIZE A