


A1C25-A
ACTUAL SIZE



PANDUIT PART NUMBER*	NOMINAL CABLE O.D. in./ (mm)	A in. (mm)	B in. (mm)	C in. (mm)	STATIC LOAD** lbs./ (g)	WEIGHT lbs./ (g) 100 pcs.
A1C12-A	0.120 (3.0)	0.77 (19.6)	0.12 (3.0)	0.23 (5.8)	0.14 (64)	0.21 (95)
A1C25-A	0.250 (6.4)	0.91 (23.1)	0.25 (6.4)	0.38 (9.7)	0.14 (64)	0.32 (145)
A1C38-A	0.375 (9.5)	1.04 (26.4)	0.38 (9.7)	0.51 (13.0)	0.14 (64)	0.42 (190)
A1C50-A	0.500 (12.7)	1.17 (29.7)	.50 (12.7)	0.64 (16.3)	0.14 (64)	0.50 (227)

TO APPLY MOUNT

- NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

CAD FILENAME/LAYERS

GB0431BA_PB_A1CCLIPS_02

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

A1C-A
ADHESIVE CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
(.XX) ± 0.05 (1.3) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY SJSU

MAT'L:	
--------	--

DATE	11-5-93
------	---------

CHK'D	
-------	--

GRAY
PVC

SCALE	NONE
-------	------

DRAWING NO.

GB0431BA

DWG
A
SIZE

2	6/15/01	LGG		ADDED REF TO DIM	GB0431BA	2				
1	2-16-94	SJSU		REVERSE TEAR TAB	GB0431BA	1				
R	11-5-93	SJSU		INITIAL RELEASE	GB0431BA	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		