


A2C25-A
ACTUAL SIZE



PANDUIT PART NUMBER*	NOMINAL CABLE O.D. in./ (mm)	A in. (mm)	B in. (mm)	C in. (mm)	STATIC LOAD** lbs./ (g)	WEIGHT lbs./ (g) 100 pcs.
A2C12-A	0.120 (3.0)	1.30 (33.0)	0.12 (3.0)	0.23 (5.8)	0.37 (168.6g)	0.28 (127)
A2C25-A	0.250 (6.4)	1.43 (36.3)	0.25 (6.4)	0.36 (9.1)	0.37 (168.6g)	0.29 (132)
A2C38-A	0.375 (9.5)	1.56 (39.6)	0.38 (9.7)	0.49 (12.4)	0.37 (168.6g)	0.34 (154)
A2C50-A	0.500 (12.7)	1.72 (43.7)	0.50 (12.7)	0.61 (15.5)	0.37 (168.6g)	0.39 (177)

TO APPLY MOUNT

- 1) REMOVE PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION.
- 3) APPLY PRESSURE TO MOUNT.

NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS	
---------------------	--

G00432BB_PB_A2CCLIPS_02

PANDUIT

CORP. TINLEY PARK, ILLINOIS

A2C-A
ADHESIVE CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
(.XX) ± 0.05 (1.3) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	
------------------------	--

MAT'L:

SCALE	NONE
-------	------

DATE	12-2-96
------	---------

GRAY
PVC

DRAWING NO.
GB0432BB

DWG
A
SIZE

2	5/10/02	LGG		CHG STATIC LOAD. WAS .29(132)	GB0432BB	2				
I	6/15/01	LGG		ADDED "REF" TO DIM	GB0432BB	I				
R	12-2-96	RJKO		INITIAL RELEASE. REPLACED CUSTOMER DRAWING NO. 34025-10.	GB0432BB	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		