




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

| PANDUIT<br>PART<br>NUMBER | DIMENSIONS     |                |                |                         | MAXIMUM<br>CABLE DIA.<br>in. (mm) | ADHESIVE<br>BACKING  | WEIGHT<br>lbs/100 pcs<br>(g)/100 pcs |
|---------------------------|----------------|----------------|----------------|-------------------------|-----------------------------------|----------------------|--------------------------------------|
|                           | A              | B              | C              | D                       |                                   |                      |                                      |
| ACC38-A                   | 1.00<br>(25.4) | 1.00<br>(25.4) | 0.49<br>(12.4) | 0.40<br>(10.2)<br>(REF) | 0.380<br>(9.6)                    | RUBBER               | 0.40<br>(181)                        |
| ACC38-AT                  |                |                |                |                         |                                   | ACRYLIC              |                                      |
| ACC38-AV                  |                |                |                |                         |                                   | HIGH BOND<br>ACRYLIC |                                      |



TWO UP CONFIGURATION  
(AS SUPPLIED TO CUSTOMER)

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

|                                                                                                                                    |                         |                                                                                              |               |
|------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------------------------------------------------------------------------------|---------------|
| CAD FILENAME/LAYERS                                                                                                                |                         | G03597BB_DC_GB0239DY/00C                                                                     |               |
| <b>PANDUIT</b> CORP.                                                                                                               |                         | TINLEY PARK, ILLINOIS                                                                        |               |
| ACC38-A, ACC38-AT, ACC38-AV                                                                                                        |                         | ADHESIVE CORD CLIP                                                                           |               |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)<br>(.XX) ±0.02 (.5) ANGLES ±5° |                         | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION |               |
| DRAWN BY<br>MLD                                                                                                                    | MAT'L:<br>NYLON 6/6     |                                                                                              | SCALE<br>FULL |
| DATE<br>8-8-96                                                                                                                     | DRAWING NO.<br>GB0239DY |                                                                                              | DWG<br>A      |
| CHK'D<br>KCN                                                                                                                       | SIZE                    |                                                                                              |               |

|     |          |      |     |                                                                                                                                                                                                                    |          |     |      |     |  |
|-----|----------|------|-----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|-----|------|-----|--|
| 00C | 11-6-09  | TMSA | SMY | ADDED ACC38-AV PART NUMBER                                                                                                                                                                                         | GB0239DY | 00C | KCN  |     |  |
| 00B | 6/23/08  | DJSM |     | REVISED AND RE-RELEASED TO TEAMCENTER<br>REV HISTORY; TABULARIZED DIMS, REMOVED<br>.45 AND .27 DIMS, REVISED .38 DIM TO<br>INCLUDE TAPE, TIGHTENED TOLERANCES,<br>REMOVED APPLICATION, TAPE, AND<br>WARRANTY NOTES | GB0239DY | 00B |      |     |  |
| I   | 10/30/00 | CGSM |     | CHANGED DIMS TO REF, REMOVED .03 DIM,<br>CHANGED APPLICATION NOTE 1                                                                                                                                                | GB0239DY | I   |      |     |  |
| R   | 8-8-96   | MLD  |     | INITIAL RELEASE                                                                                                                                                                                                    | GB0239DY | R   |      |     |  |
| REV | DATE     | BY   | CHK | DESCRIPTION                                                                                                                                                                                                        | ECN      | R   | CUST | SUP |  |