




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

| PANDUIT PART NUMBER | DIMENSIONS     |                |               |                         | MAXIMUM CABLE DIA.<br>in. (mm) | ADHESIVE BACKING  | WEIGHT<br>lbs/100 pcs<br>(g)/100 pcs |
|---------------------|----------------|----------------|---------------|-------------------------|--------------------------------|-------------------|--------------------------------------|
|                     | A              | B              | C             | D                       |                                |                   |                                      |
| ACC62-A             | 1.12<br>(28.5) | 1.24<br>(31.4) | .73<br>(18.5) | 0.65<br>(16.5)<br>(REF) | 0.62<br>(15.7)                 | RUBBER            | 0.96<br>(437)                        |
| ACC62-AT            |                |                |               |                         |                                | ACRYLIC           |                                      |
| ACC62-AV            |                |                |               |                         |                                | HIGH BOND ACRYLIC |                                      |



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

CAD FILENAME/LAYERS: G03597BD\_DC\_GB0239BB/00C

**PANDUIT** CORP.

TINLEY PARK, ILLINOIS

ACC62-A, ACC62-AT, ACC62-AV  
ADHESIVE CORD CLIP

| REV | DATE    | BY   | CHK | DESCRIPTION   | ECN      | R   | CUST | SUP |
|-----|---------|------|-----|---|----------|-----|------|-----|
| 00C | 11-6-09 | TMSA | SMY | ADDED PART NUMBER ACC62-AV  | GB0239BB | 00C | KLN  |     |
| 00B | 7/9/08  | DJSM |     | REVISED AND RE-RELEASED TO TEAMCENTER<br>REV HISTORY; TABULARIZED DIMS;<br>REMOVED .86 AND .49 DIMS; REVISED .63<br>DIM TO INCLUDE TAPE; .73 WAS .74;<br>REMOVED TAPE, APPLICATION, AND<br>WARRANTY NOTES | GB0239BB | 00B |      |     |
| 3   | 7/18/00 | JAD  |     | DIMENSIONS, .63, .86, & .49 WERE<br>CHANGED TO REF DIMENSIONS   | GB0239BB | 3   |      |     |

|  |                     |  |                  |
|--|---------------------|--|------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)<br>(.XX) ±0.02 (.5) ANGLES ±5° |                     | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION |                  |
| DRAWN BY<br>JRL  | MAT'L:<br>NYLON 6/6 | SCALE<br>FULL  |                  |
| DATE<br>9-11-92  | CHK'D<br>KLN        | DRAWING NO.<br>GB0239BB  | DWG<br>SIZE<br>A |