


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DIMENSIONS			
	'A'	'B' (REF)	'C'	'D'
HBN.75	0.075 (1.905)	1.40 (35.56)	0.62 (15.75)	0.75 (19.05)
HBN1		1.65 (41.91)		1.00 (25.4)
HBN1.5	0.084 (2.134)	2.16 (54.86)		1.50 (38.1)
HBN2	0.093 (2.362)	2.66 (67.56)		2.00 (50.8)
HBN2.5	0.107 (2.718)	3.16 (80.26)		2.50 (63.5)
HBN3	0.122 (3.099)	3.67 (93.22)		3.00 (76.2)
HBN4	0.142 (3.607)	4.67 (118.62)		4.00 (101.6)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS, PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G00239KB\_PB\_HBN\_01

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

HBN - HARNESS BOARD NAIL

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.XX) ± 0.100 (2.54) (XXX) ± 0.010 (0.25)  
ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 4/10/03

NICKEL PLATED  
STEEL

DRAWING NO.

G00239KB

DWG  
SIZE  
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	2/28/06	JAD		MODIFY TOL FOR .XX DIM'S--WAS 0.06 REVISED DIM 'B' ALL P/N'S	G00239KB	1		