



ADHESIVE BACKING
PRESSURE SENSITIVE
FOAM .040 (1.0) THICK
WITH PROTECTIVE LINER.

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. SEE TABLE.

Technical drawing of a cross-section of a mechanical part. The drawing shows a profile with a rounded top and a central cavity. Dimensions are indicated with arrows and text:

- Top horizontal dimension: 0.47 (11.9) REF.
- Internal horizontal dimension: REF. 0.62
- Bottom horizontal dimension: 0.78

G00430BB_PB_LC3_A_02

TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

AT'L:

RIGID PVC

A
SIZE

2	6-29-01	LGG		UPDATED AND ADDED REF.	GB0430BB	2				
1	6-2-98	MLD		MADE OVERALL HEIGHT DIM A REF. DIM	GB0430BB	1				
				CHANGED CAD FILE NAME FROM GB0430BB_PB_LC3_A_00						
R	03/29/94	SJSU		INITIAL RELEASE	GB0430BB	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		