



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MAX. BUNDLE DIA. in/mm	RECM. FASTENER	WEIGHT lb/g/100 pcs
RER.75-S6	0.75 (19.0)	#6 SCRW. (M3)	2.1 (953.4)

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G00239IN_PB_RER.75_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

ELASTIC RETAINER, RER.75-S6

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± N/A (.XXX) ± N/A
(.XX) ± .020(.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

1	7/21/03	JAD		REVISED ARM MATERIAL	G80239IN	1				DRAWN BY	LGG	MAT'L:	NYLON BASE & RUBBER MODIFIED NYLON 6/6 ARM	SCALE	FULL
R	6/19/01	LGG		INITIAL RELEASE-REPLACED SS-6214	G80239IN	R				DATE	6/19/01			DRAWING NO.	GB0239IN
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D				DWG SIZE	A