THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. *	RECOMMENDED FASTNER	RECOMMENDED CABLE TIE	WEIGHT lbs. / 100 pcs (g) / 100 pcs
PPF2SV-S25-_	1/4" [6mm]	TAK-TY or HOOK & LOOP	3.25 (1474.2)





NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.



SCALE: 3/4

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS: G02386BA_PB_PPF2SV_01

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-POST (FLAT) (PPF2SV-___-_)

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]
(.XX) ±0.02 [0.5] ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JAD
DATE: 6/5/00
CHK'D:
MAT'L: NYLON 6/6
SCALE: 1/2
DRAWING NO.: GB2386BA
DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
1	8/14/01	LGG		UPDATED AND ADDED 'REF'	GB2386BA 1		
R	6/5/00	JAD		INITIAL RELEASE	GB2386BA R		