





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	DIMENSIONS									WEIGHT lbs. (grams)
	A	B	C	D	E	F	G	H	J	
CMW-KIT	2.00 (50.8)	1.00 (25.4)	5.25 (133.4)	9.58 (243.3)	1.75 (44.4)	3.00 (76.2)	1.20 (30.5)	3.33 (84.6)	4.87 (124.5)	.606 (274.9)
CMWB	—	—	5.24 (133.4)	—	1.75 (44.4)	—	1.20 (30.5)	—	—	.230 (104.3)
CMWW	2.00 (50.8)	1.00 (25.4)	—	—	—	3.00 (76.2)	—	3.33 (84.6)	4.87 (124.5)	.188 (85.3)

Notes:

1. See current price sheet for part number suffix designation for package size and color.
2. Flame retardant cable ties (Qty. 3, PLT2S-M60) included with CMWB and CMW-KIT.



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G02249MC_PB_CMW_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

CABLE MANAGEMENT WATERFALL
(CMW-KIT, CMWB, CMWW)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (,.XXX) ±0.010 (0.25)
(.XX) ±0.03 (0.8) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

I	4/16/03	LGG		CHG DIM C & D FOR CMW-KIT WAS 5.24(133.4) & 9.60(243.3). ADD 'REF' TO DIM 'A'	GB2249MC	I				DRAWN BY	KLN	MAT'L: GLASS REINFORCED FLAME RETARDANT NYLON 6/6	SCALE 1/4		
R	2/1/01	KLN		INITIAL RELEASE	GB2249MC	R				DATE	2/1/01		DRAWING NO.	GB2249MC	CHK A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		CHK'D						