

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


HSTTP 12 - M

PANDUIT NUMBERING SYSTEM

LENGTH M = 1000' MIN.  
 D = 500' MIN.  
 TL = 250' MIN.  
 C = 100' MIN.

EXPANDED I.D. TUBING SIZE.

PVC THIN WALL HEAT SHRINK TUBING.



| PANDUIT PART NUMBER | Min. RECOVERED ID | Max. RECOVERED ID | NOMINAL REC WALL THICKNESS [in. (mm)] |
|---------------------|-------------------|-------------------|---------------------------------------|
| HSTTP05-M           | .046 (1.2)        | .023 (.6)         | .020 (0.5)                            |
| HSTTP06-M           | .063 (1.6)        | .031 (.8)         | .020 (0.5)                            |
| HSTTP09-M           | .093 (2.4)        | .046 (1.2)        | .025 (0.6)                            |
| HSTTP12-M           | .125 (3.2)        | .062 (1.6)        | .025 (0.6)                            |
| HSTTP19-M           | .187 (4.8)        | .093 (2.4)        | .025 (0.6)                            |
| HSTTP25-M           | .250 (6.4)        | .125 (3.2)        | .025 (0.6)                            |
| HSTTP38-D           | .375 (9.5)        | .187 (4.8)        | .030 (0.8)                            |
| HSTTP50-D           | .500 (12.7)       | .250 (6.4)        | .030 (0.8)                            |
| HSTTP75-C           | .750 (19.0)       | .375 (9.5)        | .035 (0.9)                            |
| HSTTP100-TL         | 1.000 (25.4)      | .500 (12.7)       | .040 (1.0)                            |
| HSTTP150-C          | 1.500 (38.1)      | .750 (19.0)       | .045 (1.1)                            |
| HSTTP200-C          | 2.000 (50.8)      | 1.000 (25.4)      | .050 (1.3)                            |

**NOTES:**

1. MATERIAL: CROSS-LINKED, FLEXIBLE, HIGHLY FLAME RETARDANT.
2. COLOR: BLACK
3. SHRINK RATIO: 2:1
4. SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO DIMENSIONAL TABLE FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S
5. "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

|   |   |
|---|---|
| DIMENSIONS IN BRACKETS ARE METRIC [ mm ]  |   |
| CAD FILENAME/LAYERS G00239K1_PB_HSTTP_01  |   |
|   |   |
| HSTTP PVC THIN WALL HEAT SHRINK   |   |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:<br>(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)<br>(.XX) ±0.02 (0.5) ANGLES ± 5° | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. |
| DRAWN BY LGRAVITT   | MAT'L: NONE   |
| DATE 5/12/03  | SEE NOTES   |
| CHK'D   | DWG SIZE A  |
| DRAWING NO. G00239K1  |   |

|     |         |     |     |                          |          |   |      |     |
|-----|---------|-----|-----|--------------------------|----------|---|------|-----|
| 1   | 2/23/06 | JAD |     | HSTTP75-C WAS HSTTP75-TL | GB0239K1 | 1 |      |     |
| REV | DATE    | BY  | CHK | DESCRIPTION              | ECN      | R | CJST | SUP |