



PANDUIT PART NUMBER	USED WITH CABLE TIES	DIMENSIONS				MATERIAL	WEIGHT grams/100pcs
		'A' (REF)	'B' (REF)	'C' (REF)	'D' (REF)		
PUM-100--30	M, I, S	16.2	6.6	16.9	10.4	HEAT STABILIZED NYLON 6/6 BLACK	70.07


1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.

2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.

3. APPLICATION SPECIFICATION:
HOLE DIAMETER: 9.0 - 10.0 mm
PANEL THICKNESS: 0.8 - 7.0 mm



SCALE 2:1



06B	9-26-08	PSG	ADDED, REMOVED, & RENAMED DIMENSIONS	GB0239MM	06B		
06A	8-22-08	PSG	REMOVED 2 DIMS, REMOVED RIBS FROM HEAD, UPDATED FILE NAME AND CHANGED REV STYLE	GB0239MM	06A		
R	8-24-06	TMSA	INITIAL RELEASE	GB0239MM	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP

UNLESS OTHERWISE SPECIFIED, ALL
DIMENSIONS ARE METRIC
TOLERANCE: $\pm 0.5\text{MM}$

PUM-100-30
PUSH UMBRELLA MOUNT 100

PANDUIT
CORP.

TINLEY PARK, ILLINOIS

G03151BD_DC_GB0239MM/06B

CAD FILENAME/LAYERS

DRAWN BY
TMSA

MAT'L:

SCALE
1 : 1 UNLESS NOTED

SEE TABLE

DRAWING NO.

REV	DATE	BY	CHK	DESCRIPTION
-----	------	----	-----	-------------

ECN -

CUST

SUP

OK'D

כח

GB0239MM

A
S175