



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

*PANDUIT PART NUMBER	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS / 100 FT (g)
T12R	.125 (3.2)	.218±.047 (5.5±1.2)	.030±.006 (0.8±0.2)	0.4 (181.4)
T19R	.188 (4.8)	.250±.047 (6.4±1.2)	.035±.008 (0.9±0.2)	0.7 (320.1)
T25R	.250 (6.4)	.375±.047 (9.5±1.2)	.040±.008 (1.0±0.2)	1.1 (499.0)
T38R	.375 (9.5)	.437±.047 (11.1±1.2)	.055±.010 (1.4±0.3)	2.4 (1088.6)
T50R	.500 (12.7)	.500±.047 (12.7±1.2)	.060±.016 (1.5±0.4)	3.6 (1633.0)
T62R	.625 (15.9)	.625±.047 (15.9±1.2)	.062±.020 (1.6±0.5)	4.7 (2131.9)
T75R	.750 (19.1)	.875±.047 (22.2±1.2)	.065±.020 (1.7±0.5)	6.0 (2721.6)
T100R	1.000 (25.4)	1.125±.047 (28.6±1.2)	.070±.020 (1.8±0.5)	8.8 (3991.7)

△C



- \* Notes:
- 1) See current price sheet for part number suffix designations, package size and part color.
  - △A 2) For roll sizes larger than 10 ft., splicing may occur.
  - △B 3) Reverse Cut.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G03597BJ\_DC\_GB0239LQ\_02/00A

**PANDUIT**

CORP. TINLEY PARK, ILLINOIS

(FIRE RESISTANT) SPIRAL WRAP  
△ (CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ±..... (,XXX) ±.....  
(.XX) ±..... ANGLES ±.....

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
02	5/23/11	LEF	VJS	C REVISE PANDUIT PART NUMBER D TITLE BLOCK CHANGE TO FIRE RESISTANT	GB0239LQ	02	RAMI	
01	5/10/11	LEF	VJS	A REMOVER PHONE NUMBER FROM NOTE 2 B ADDED NOTE 3 REVERSE CUT	GB0239LQ	01	RAMI	
R	5/12/05	JAD		INITIAL RELEASE	GB0239LQ	R		

DRAWN BY  
JAD

MAT'L:

DATE  
5/12/05

POLYETHYLENE

CHK'D  
JVL

SCALE  
NONE

DRAWING NO.  
GB0239LQ

DWG  
SIZE  
A