






PANDUIT PART NO.*	DIMENSIONS			USE WITH ANY OF THESE CABLE TIES	WEIGHT lbs / 100 (g) / pcs.
	"A"	"B"	"C"		
TM3-X2-__	0.87 (22.10)	0.75 (19.05)	0.62 (15.75)	M, I, S, LH	0.97 (439.9)
TM1-X2-__	0.52 (13.21)	0.46 (11.68)	0.32 (8.13)	M	0.17 (77.1)



ROTATED 90°

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR OPTIONS.
- CABLE TIE CROSS-SECTION CODE:
M = MINATURE
I = INTERMEDIATE
S = STANDARD
LH = LIGHT HEAVY
- MOUNT MATERIAL:
TM3-X2-_0 WEATHER RESISTANT NYLON 6/6
COLOR: BLACK
-_76 OR
TEFZEL COLOR: BLUE/GREEN
TM1-X2-_ NYLON 6/6, COLOR: NATURAL
RIVET MATERIAL: 5056-S ALUMINUM

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G02446BA_PC_TM-X2_04

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

SWIVEL TIE MOUNT
(TM_-X2-__)UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

JAD

MAT'L:

SCALE

1.5X

DATE

11/01/00

SEE NOTE 3

DRAWING NO.

GB2446BA

DWG

A
SIZE

4	3/10/06	JAD		ADD REF FOR -76 TM3 PART	GB2446BA	4			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	