




PANDUIT PART NO.	A	B (REF)	C	D (REF)	LOOP TENSILE
HLTT1.5S	7.00 (178)	5.02 (127.5)	.75 (19.0)	.5 (12.7)	30LBS MIN. (133 N)



NOTES:

1. COLOR: BLACK LOOP/NATURAL MICROHOOK
2. TEMP. LIMITS: 50C CONTINUOUS
3. RoHS COMPLIANT
4. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
5. MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
6. LOOP: POLYAMIDE; MICROHOOK: POLYPROPYLENE; ADHESIVE: REMOVABLE PRESSURE SENSITIVE TYPE DESIGNED TO LEAVE NO RESIDUE ON CABLE BUNDLE.
7. TABLE DIMS ARE IN.(MM).

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
00A	1/25/11	DFA	DJW	RELEASED FOR PRODUCTION	10K011AD_DC	00A	GLZ	

CAD FILENAME/LAYERS		10K011AD_DC/00A	
<h1>PANDUIT</h1> CORP TINLEY PARK, ILLINOIS			
<h2>HLTT1.5S</h2> TAPE TY			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.15 (3.8) (.XXX) ±.03 (.8) (.XX) ±.05 (1.3) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY DFA	MAT'L: SEE NOTE 6	SCALE FULL	
DATE 1/25/11	CHK'D GLZ	DRAWING NO. 10K011AD_DC	DWG B SIZE